

Kimtech* A5 Sterile Cleanroom Apparel

Product Information

| Code | Description | Color | Size | Case/Pack |
|----------|---|-------|-----------|-----------|
| 88800 | Coverall | White | Small | 25/case |
| 88801 | Coverall | White | Medium | 25/case |
| 88802 | Coverall | White | Large | 25/case |
| 88803 | Coverall | White | XL | 25/case |
| 88804 | Coverall | White | 2XL | 25/case |
| 88805 | Coverall | White | 3XL | 25/case |
| 88806 | Coverall | White | 4XL | 25/case |
| 12917 | Coverall | White | 5XL | 25/case |
| 12914 | Coverall | White | 6-8XL | 25/case |
| 25797 | Hood w/ties | White | Universal | 100/case |
| 88807-10 | Hood | White | Universal | 100/case |
| 36072 | Integrated Hood & Mask | White | Universal | 75/case |
| 47677 | Integrated Hood & Mask | White | XL | 75/case |
| 36077 | Sleeve Protector, 18" | White | Universal | 100 pairs |
| 31683 | Boots w/Grasp ties & vinyl trimmed edge | White | SM / MD | 100 pairs |
| 31696 | Boots w/Grasp ties & vinyl trimmed edge | White | Universal | 100 pairs |
| 31697 | Boots w/Grasp ties & vinyl trimmed edge | White | XL / 2XL | 100 pairs |
| 12922 | Boots w/Ties | White | SM/MD | 100 pairs |
| 88888 | Boots w/Ties | White | Universal | 100 pairs |
| 12920 | Boots w/Ties | White | XL/2XL | 100 pairs |
| | | | | |



| Additional Attributes | | | | | |
|-----------------------|--|--|--|--|--|
| • | 100% Polypropylene Breathable SMS Fabric | | | | |
| • | Suited for ISO Class 5 or higher cleanrooms | | | | |
| • | CE Marked - Category III, PPE | | | | |
| • | Manufactured in ISO9001 2000 facility | | | | |
| • | Triple-bagged, vacuum packaged, includes sterility indicator | | | | |
| • | Folded inside out for aseptic donning, blue indicator line on interior | | | | |
| • | Expiration Date – 5 years | | | | |
| • | Certificate of Conformance available online at www.kimtech.com/certificates | | | | |
| • | Certificate of Irradiation available online at www.kimtech.com/certificates | | | | |
| • | Coveralls – Bound seams & REFLEX* Design – www.kcprofessional.com | | | | |
| • | Coveralls and Sleeves - Tunneled elastics and Thumbs loops | | | | |
| • | Boots - Vinyl Sole, Serged Seams | | | | |
| • | Boots w/Grasp ties - Vinyl trimmed edges; ties attached at foot for better fit | | | | |

Workmanship Requirements: Apparel shall be made in accordance with reasonable industry practice with respect to defects, dirt and contamination. Apparel should be packaged as specified, having described size, and in the appropriate quantity as listed.

For Additional information: Contact your Kimberly-Clark representative, our Customer Service Team (888)-346-GOKC (4652) or KCPInfo@kcc.com

KIMTECH PURE* A5 Hood Technical Data

| Property Property | Units | Target | Standards |
|--|-----------------|------------------|-----------------------|
| | | | 0.10.11.0.00 |
| Bacterial Filtration Efficiency (3.0µ), prior to sterilization | % | 98 | ASTM F2100 |
| Particle Filtration Efficiency (0.5µ), prior to sterilization | % | 93 | ASTM F2299† |
| Sterilization (SAL1) – Gamma Irradiated | - | 10 ⁻⁶ | ANSI/AAMI/ISO 11137 |
| Trap Tear, MD | lb _f | 18.0 | ASTM D5722, IST 100.2 |
| Trap Tear, CD | lb _f | 10.0 | ASTM D5722, IST 100.2 |
| Grab Tensile, MD | lb _f | 41 | ASTM D5034 |
| Grab Tensile, CD | lb _f | 28 | ASTM D5034 |
| Hydrostatic Head | cm H₂O | 118 | AATCC-127 |
| Air Permeability | cfm | 425 | ASTM D737, IST 70.1 |
| Flammability | = | Class 1 | 16 CFR 1610 |
| Particle Shedding (Helmke Drum) | - | Category 1 | IEST-RP-CC003.3 |

† Non-neutralized aerosol

¹ Sterility Assurance Level

Rev.10/2017

