

Sterile PolySat®

Propropylene Wipers

TECHNICAL DATA SHEET



Features

- Gamma irradiated to 10⁻⁶ Sterility Assurance Level, according to AAMI Guidelines ensures sterility
- ► Lot-specific information on each shipment simplifies record keeping:
 - Certificate of Irradiation confirms radiation dosage.
 - Certification of Compliance, and
 - Expiration date marked on each package
- Pre-wetted with 70% isopropyl alcohol/30% deionized water, filtered through a 0.2µm filter
- ▶ 100% melt-blown polypropylene substrate
- Independent quality control audits for sterility assurance

Polypropylene wipers pre-wetted with 70% isopropyl alcohol and sterilized

Description

Sterile PolySat® is constructed from a 100% melt-blown polypropylene substrate that is pre-wetted with 70% isopropyl alcohol and packaged in a resealable FlexPack. Each package is gamma irradiated to 10⁻⁶ Sterility Assurance Level to AAMI Guidelines.

Sterile PolySat® is used for alcohol wiping in sterile environments in pharmaceutical aseptic fill areas, biotechnology manufacturing facilities, microbiological laboratories, sterile suites and prep rooms.

Applications

- Designed for cleaning and polishing equipment and environmental surfaces during and following the production flow
- ► Ideal for easy cleanup of soiled surfaces
- ► Suitable for sterile wiping of production equipment requiring low
- solvent extractables and low particle generation

Benefits

- Optimizes solution usage and reduces spill potential
- Eliminates problems associated with filtration, sterilization and mixing of alcohol and DI water
- Packaging permits alcohol wipedown of exterior bag before introduction into sterile suites
- ► Soft, versatile wiping substrate
- Assures quality of individual lots and sterility assurance through expiration date

Products

Number	Description	Packaging
TX3213	Sterile PolySat® 9" x 11" (23 cm x 28 cm) polypropylene wipers pre-wetted with 70% IPA	50 wipers/flexpack; 24 flexpacks/case
TX3216	Sterile PolySat® 9" x 11" (23 cm x 28 cm) polypropylene wipers pre-wetted with 70% IPA	20 wipers/flexpack; 24 flexpacks/case

North America: 1210 South Park Drive, Kernersville, NC 27284 • Tel 336.996.7046 • Fax 336.996.2297

Europe/Middle East: Saffierlaan 5, 2132 VZ Hoofddorp, The Netherlands • Tel +31 88 1307 400 • Fax +31 88 1307 499

Asia/Pacific: ITW Singapore (Pte) Ltd., 500 Chai Chee Lane, Singapore 469024 • Tel +65 6468 9433 • Fax +65 6468 6772